

Tabela produktów, których dotyczy problem

Kod produktu	Opis produktu	Numer serii
107142	Prismaflex HF1400 set	18C0204
107142	Prismaflex HF1400 set	18C0804
107142	Prismaflex HF1400 set	18C1604
107142	Prismaflex HF1400 set	18C2706
107142	Prismaflex HF1400 set	18D0904
107142	Prismaflex HF1400 set	18D1704
107142	Prismaflex HF1400 set	18D2604
107142	Prismaflex HF1400 set	18E1406
107142	Prismaflex HF1400 set	18E2402
107142	Prismaflex HF1400 set	18E2901
107142	Prismaflex HF1400 set	18F0801
107142	Prismaflex HF1400 set	18F1303
107142	Prismaflex HF1400 set	18F2003
107142	Prismaflex HF1400 set	18F2902
107142	Prismaflex HF1400 set	18G1103
107142	Prismaflex HF1400 set	18G1804
107142	Prismaflex HF1400 set	18H2301
107142	Prismaflex HF1400 set	18H3003
107142	Prismaflex HF1400 set	18I1302
107142	Prismaflex HF1400 set	18I1703
107142	Prismaflex HF1400 set	18I2405
107142	Prismaflex HF1400 set	18J0404
107142	Prismaflex HF1400 set	18J2305
107142	Prismaflex HF1400 set	18J2506
107142	Prismaflex HF1400 set	18K0701
107142	Prismaflex HF1400 set	18K1508
107142	Prismaflex HF1400 set	18K2103
107142	Prismaflex HF1400 set	18K3002
107142	Prismaflex HF1400 set	18L0401
107142	Prismaflex HF1400 set	18L0601
107142	Prismaflex HF1400 set	19A1601
107142	Prismaflex HF1400 set	19A2902
107142	Prismaflex HF1400 set	19A3001
107144	Prismaflex TPE 2000 set	18C1904
107144	Prismaflex TPE 2000 set	18E2306
107144	Prismaflex TPE 2000 set	18E2804
107144	Prismaflex TPE 2000 set	18F0401
107144	Prismaflex TPE 2000 set	18F1104

107144	Prismaflex TPE 2000 set	18F1803
107144	Prismaflex TPE 2000 set	18F2703
107144	Prismaflex TPE 2000 set	18G1203
107144	Prismaflex TPE 2000 set	18G1803
107144	Prismaflex TPE 2000 set	18G2305
107144	Prismaflex TPE 2000 set	18H2803
107144	Prismaflex TPE 2000 set	18I0304
107144	Prismaflex TPE 2000 set	18I1303
107144	Prismaflex TPE 2000 set	18I1804
107144	Prismaflex TPE 2000 set	18J1901
107144	Prismaflex TPE 2000 set	18J2905
107144	Prismaflex TPE 2000 set	18K0208
107144	Prismaflex TPE 2000 set	18K1302
107144	Prismaflex TPE 2000 set	18K2005
107144	Prismaflex TPE 2000 set	18L0602A
107144	Prismaflex TPE 2000 set	18L1004
107144	Prismaflex TPE 2000 set	19A0803
107144	Prismaflex TPE 2000 set	19A1504A
107144	Prismaflex TPE 2000 set	19A2107
107144	Prismaflex TPE 2000 set	19B0104
107144	Prismaflex TPE 2000 set	19B0411
107636	prismaflex ST100 set	18C1501
107636	prismaflex ST100 set	18C2305
107636	prismaflex ST100 set	18D0306
107636	prismaflex ST100 set	18D1805
107636	prismaflex ST100 set	18D2403
107636	prismaflex ST100 set	18E1603
107636	prismaflex ST100 set	18E2302
107636	prismaflex ST100 set	18F0802
107636	prismaflex ST100 set	18F1105
107636	prismaflex ST100 set	18F1902
107636	prismaflex ST100 set	18F2704
107636	prismaflex ST100 set	18G1104
107636	prismaflex ST100 set	18G2001
107636	prismaflex ST100 set	18G2401
107636	prismaflex ST100 set	18I1407
107636	prismaflex ST100 set	18J2303
107636	prismaflex ST100 set	18K1303
107636	prismaflex ST100 set	18L0405
107636	prismaflex ST100 set	18L0802
107636	prismaflex ST100 set	19A0304

107636	prismaflex ST100 set	19A2403
107636	prismaflex ST100 set	19B1601
107636	prismaflex ST100 set	19B1806
107636	prismaflex ST100 set	19B2505
107640	Prismaflex ST150 set	18C0102Z
107640	Prismaflex ST150 set	18C0201Z
107640	Prismaflex ST150 set	18C0205
107640	Prismaflex ST150 set	18C0301
107640	Prismaflex ST150 set	18C0603
107640	Prismaflex ST150 set	18C0605
107640	Prismaflex ST150 set	18C0903
107640	Prismaflex ST150 set	18C1203
107640	Prismaflex ST150 set	18C1205
107640	Prismaflex ST150 set	18C1301
107640	Prismaflex ST150 set	18C1302
107640	Prismaflex ST150 set	18C1401
107640	Prismaflex ST150 set	18C1601
107640	Prismaflex ST150 set	18C1903
107640	Prismaflex ST150 set	18C2002
107640	Prismaflex ST150 set	18C2105
107640	Prismaflex ST150 set	18C2902
107640	Prismaflex ST150 set	18C3003
107640	Prismaflex ST150 set	18D0402
107640	Prismaflex ST150 set	18D0503
107640	Prismaflex ST150 set	18D0602
107640	Prismaflex ST150 set	18D1102
107640	Prismaflex ST150 set	18D1201
107640	Prismaflex ST150 set	18D1301
107640	Prismaflex ST150 set	18D1308
107640	Prismaflex ST150 set	18D1804
107640	Prismaflex ST150 set	18D1904
107640	Prismaflex ST150 set	18D2404
107640	Prismaflex ST150 set	18D2504
107640	Prismaflex ST150 set	18D2605
107640	Prismaflex ST150 set	18D3001
107640	Prismaflex ST150 set	18E0202
107640	Prismaflex ST150 set	18E0301
107640	Prismaflex ST150 set	18E0402
107640	Prismaflex ST150 set	18E0405
107640	Prismaflex ST150 set	18E0701
107640	Prismaflex ST150 set	18E1504

107640	Prismaflex ST150 set	18E1604
107640	Prismaflex ST150 set	18E1705
107640	Prismaflex ST150 set	18E1802
107640	Prismaflex ST150 set	18E2304
107640	Prismaflex ST150 set	18E2504
107640	Prismaflex ST150 set	18E2902
107640	Prismaflex ST150 set	18E2903
107640	Prismaflex ST150 set	18E3004
107640	Prismaflex ST150 set	18E3102
107640	Prismaflex ST150 set	18F0404
107640	Prismaflex ST150 set	18F0605
107640	Prismaflex ST150 set	18F0705
107640	Prismaflex ST150 set	18F1202
107640	Prismaflex ST150 set	18F1404
107640	Prismaflex ST150 set	18F1903
107640	Prismaflex ST150 set	18F2004
107640	Prismaflex ST150 set	18F2202
107640	Prismaflex ST150 set	18F2604
107640	Prismaflex ST150 set	18F2804
107640	Prismaflex ST150 set	18F2904
107640	Prismaflex ST150 set	18G0303
107640	Prismaflex ST150 set	18G0406
107640	Prismaflex ST150 set	18G0506
107640	Prismaflex ST150 set	18G0602
107640	Prismaflex ST150 set	18G1102
107640	Prismaflex ST150 set	18G1202
107640	Prismaflex ST150 set	18G1302
107640	Prismaflex ST150 set	18G1303
107640	Prismaflex ST150 set	18G1802
107640	Prismaflex ST150 set	18G1902
107640	Prismaflex ST150 set	18G2402
107640	Prismaflex ST150 set	18G2502
107640	Prismaflex ST150 set	18G2603
107640	Prismaflex ST150 set	18H2103Z
107640	Prismaflex ST150 set	18H2302
107640	Prismaflex ST150 set	18H2703Z
107640	Prismaflex ST150 set	18H2801Z
107640	Prismaflex ST150 set	18H3001
107640	Prismaflex ST150 set	18H3002
107640	Prismaflex ST150 set	18H3101
107640	Prismaflex ST150 set	18I1003

107640	Prismaflex ST150 set	18I1203Z
107640	Prismaflex ST150 set	18I1402
107640	Prismaflex ST150 set	18I1501
107640	Prismaflex ST150 set	18I1903
107640	Prismaflex ST150 set	18I2102
107640	Prismaflex ST150 set	18I2404
107640	Prismaflex ST150 set	18I2703
107640	Prismaflex ST150 set	18I2802
107640	Prismaflex ST150 set	18J0203
107640	Prismaflex ST150 set	18J0303
107640	Prismaflex ST150 set	18J0403
107640	Prismaflex ST150 set	18J0501
107640	Prismaflex ST150 set	18J0505
107640	Prismaflex ST150 set	18J1003
107640	Prismaflex ST150 set	18J1101
107640	Prismaflex ST150 set	18J1102
107640	Prismaflex ST150 set	18J1804
107640	Prismaflex ST150 set	18J1805
107640	Prismaflex ST150 set	18J1902
107640	Prismaflex ST150 set	18J2205
107640	Prismaflex ST150 set	18J2208
107640	Prismaflex ST150 set	18J2401
107640	Prismaflex ST150 set	18J2504
107640	Prismaflex ST150 set	18J3002
107640	Prismaflex ST150 set	18J3102
107640	Prismaflex ST150 set	18K0202
107640	Prismaflex ST150 set	18K0605
107640	Prismaflex ST150 set	18K0804
107640	Prismaflex ST150 set	18K1001
107640	Prismaflex ST150 set	18K1506
107640	Prismaflex ST150 set	18K1601
107640	Prismaflex ST150 set	18K1906
107640	Prismaflex ST150 set	18K2002
107640	Prismaflex ST150 set	18K2003
107640	Prismaflex ST150 set	18K2203
107640	Prismaflex ST150 set	18K2706
107640	Prismaflex ST150 set	18K2802
107640	Prismaflex ST150 set	18K3001
107640	Prismaflex ST150 set	18L0102
107640	Prismaflex ST150 set	18L0406
107640	Prismaflex ST150 set	18L0504

107640	Prismaflex ST150 set	18L0604
107640	Prismaflex ST150 set	18L0702
107640	Prismaflex ST150 set	18L0704
107640	Prismaflex ST150 set	18L1005
107640	Prismaflex ST150 set	19A0305
107640	Prismaflex ST150 set	19A0403
107640	Prismaflex ST150 set	19A0702
107640	Prismaflex ST150 set	19A0804
107640	Prismaflex ST150 set	19A0805
107640	Prismaflex ST150 set	19A1602
107640	Prismaflex ST150 set	19A1802
107640	Prismaflex ST150 set	19A2302
107640	Prismaflex ST150 set	19A2501
107640	Prismaflex ST150 set	19A2806
107640	Prismaflex ST150 set	19A2907
107640	Prismaflex ST150 set	19A3002
107640	Prismaflex ST150 set	19A3003
107640	Prismaflex ST150 set	19A3103
107640	Prismaflex ST150 set	19B0803
107640	Prismaflex ST150 set	19B0804
107640	Prismaflex ST150 set	19B1108
107640	Prismaflex ST150 set	19B1502
107640	Prismaflex ST150 set	19B1905
107640	Prismaflex ST150 set	19B2006
107640	Prismaflex ST150 set	19B2105
107640	Prismaflex ST150 set	19B2106
107640	Prismaflex ST150 set	19B2506
107640	Prismaflex ST150 set	19B2802
107640	Prismaflex ST150 set	19B2803
107642	Prismaflex Adsorba 150 kit	18E0303
107642	Prismaflex Adsorba 150 kit	19A2408
112016	OXIRIS set	18D0502
112016	OXIRIS set	18D2706
112016	OXIRIS set	18E2203A
112016	OXIRIS set	18F0604A
112016	OXIRIS set	18F2506A
112016	OXIRIS set	18G1702A
112016	OXIRIS set	18G2304A
112016	OXIRIS set	18I1102
112016	OXIRIS set	18K0504
112016	OXIRIS set	18K2603

112016	OXIRIS set	18L1803A
112016	OXIRIS set	18L1806Z
112016	OXIRIS set	19A2203
112016	OXIRIS set	19B0707
112016	OXIRIS set	19B0707Z
112017	Septex set	18G0501
112017	Septex set	18I0306
112017	Septex set	19A0402
114877	Prismaflex HP-X set	18D3002
114877	Prismaflex HP-X set	19B2005Z
114877	Prismaflex HP-X set	19B2005ZA
114877	Prismaflex HP-X set	19C0411Z
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023655
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023691
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023745
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023750
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023765
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023794
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023817
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023820
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023850
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023853
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023883
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023902
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023918
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023921
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023952
800540	MARS Treatment Kit type 1116/1 X-MARS	0000023997
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024033
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024035
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024053
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024101
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024103
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024167
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024175
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024232
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024243
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024304
800540	MARS Treatment Kit type 1116/1 X-MARS	0000024311
955503	oXiris S	18C2206
955503	oXiris S	18D0502A

955503	oXiris S	18D2706A
955503	oXiris S	18E2203
955503	oXiris S	18F0604
955503	oXiris S	18F2506
955503	oXiris S	18G1702
955503	oXiris S	18G2304
955503	oXiris S	18J0102
955503	oXiris S	18J2204
955503	oXiris S	18K0504A
955503	oXiris S	18K2603A
955503	oXiris S	18K2704
955503	oXiris S	18L1803
955503	oXiris S	18L1804
955503	oXiris S	19A2106
955503	oXiris S	19B0707A
955503	oXiris S	19C0409