

CONSERVE® SHELL	
Part Number	Description
38SC3650	CONSERVE® SUPER-FIX® SHELL36mm ID 50mm OD BEADED
38SC3852	CONSERVE® SUPER-FIX® SHELL38mm ID 52mm OD BEADED
38SC4054	CONSERVE® SUPER-FIX® SHELL40mm ID 54mm OD BEADED
38SC4256	CONSERVE® SUPER-FIX® SHELL42mm ID 56mm OD BEADED
38SC4458	CONSERVE® SUPER-FIX® SHELL44mm ID 58mm OD BEADED
38SC4660	CONSERVE® SUPER-FIX® SHELL46mm ID 60mm OD BEADED
38SC4862	CONSERVE® SUPER-FIX® SHELL48mm ID 62mm OD BEADED
38SC5064	CONSERVE® SUPER-FIX® SHELL50mm ID 64mm OD BEADED
38SC5266	CONSERVE® SUPER-FIX® SHELL52mm ID 66mm OD BEADED
38SC5468	CONSERVE® SUPER-FIX® SHELL54mm ID 68mm OD BEADED
38SC5670	CONSERVE® SUPER-FIX® SHELL56mm ID 70mm OD BEADED
38SC5672	CONSERVE® SUPER-FIX® SHELL56mm ID 72mm OD BEADED
PL38SC3852	CONSERVE® TOTAL SUPER-FIX® CUP38mm ID 52mm OD BEADED ALPHA
PL38SC4054	CONSERVE® TOTAL SUPER-FIX® CUP40mm ID 54mm OD BEADED ALPHA
PL38SC4256	CONSERVE® TOTAL SUPER-FIX® CUP42mm ID 56mm OD BEADED ALPHA
PL38SC4458	CONSERVE® TOTAL SUPER-FIX® CUP44mm ID 58mm OD BEADED ALPHA
PL38SC4660	CONSERVE® TOTAL SUPER-FIX® CUP46mm ID 60mm OD BEADED ALPHA
PL38SC4862	CONSERVE® TOTAL SUPER-FIX® CUP48mm ID 62mm OD BEADED ALPHA
38QH3644	CONSERVE® QUADRA-FIX® HA SHELL36MM ID 44MM OD
38QH3846	CONSERVE® QUADRA-FIX® HA SHELL38MM ID 46MM OD
38QH4048	CONSERVE® QUADRA-FIX® HA SHELL40MM ID 48MM OD
38QH4250	CONSERVE® QUADRA-FIX® HA SHELL42MM ID 50MM OD
38QH4452	CONSERVE® QUADRA-FIX® HA SHELL44MM ID 52MM OD
38QH4654	CONSERVE® QUADRA-FIX® HA SHELL46MM ID 54MM OD
38QH4856	CONSERVE® QUADRA-FIX® HA SHELL48MM ID 56MM OD
38QH5058	CONSERVE® QUADRA-FIX® HA SHELL50MM ID 58MM OD
38QH5260	CONSERVE® QUADRA-FIX® HA SHELL52MM ID 60MM OD
38QH5462	CONSERVE® QUADRA-FIX® HA SHELL54MM ID 62MM OD
38QH5664	CONSERVE® QUADRA-FIX® HA SHELL56MM ID 64MM OD
38QH5666	CONSERVE® QUADRA-FIX® HA SHELL56MM ID 66MM OD
38021146	CONSERVE® PLUS ORIGINAL SHELL36mm ID 46mm OD BEADED
38021148	CONSERVE® PLUS ORIGINAL SHELL38mm ID 48mm OD BEADED
38021150	CONSERVE® PLUS ORIGINAL SHELL40mm ID 50mm OD BEADED
38021152	CONSERVE® PLUS ORIGINAL SHELL42mm ID 52mm OD BEADED
38021154	CONSERVE® PLUS ORIGINAL SHELL44mm ID 54mm OD BEADED
38021156	CONSERVE® PLUS ORIGINAL SHELL46mm ID 56mm OD BEADED
38021158	CONSERVE® PLUS ORIGINAL SHELL48mm ID 58mm OD BEADED
38021160	CONSERVE® PLUS ORIGINAL SHELL50mm ID 60mm OD BEADED
38021162	CONSERVE® PLUS ORIGINAL SHELL52mm ID 62mm OD BEADED
38021164	CONSERVE® PLUS ORIGINAL SHELL54mm ID 64mm OD BEADED
38023646	CONSERVE® THICK SHELL36mm ID 46mm OD BEADED

38023848	CONSERVE® THICK SHELL38mm ID 48mm OD BEADED
38024050	CONSERVE® THICK SHELL40mm ID 50mm OD BEADED
38024252	CONSERVE® THICK SHELL42mm ID 52mm OD BEADED
38024454	CONSERVE® THICK SHELL44mm ID 54mm OD BEADED
38024656	CONSERVE® THICK SHELL46mm ID 56mm OD BEADED
38024858	CONSERVE® THICK SHELL48mm ID 58mm OD BEADED
38025060	CONSERVE® THICK SHELL50mm ID 60mm OD BEADED
38025262	CONSERVE® THICK SHELL52mm ID 62mm OD BEADED
38025464	CONSERVE® THICK SHELL54mm ID 64mm OD BEADED
38025666	CONSERVE® THICK SHELL56mm ID 66mm OD BEADED
38025668	CONSERVE® THICK SHELL56mm ID 68mm OD BEADED
SPHC0346	CONSERVE® PLUS CUP 36mm.ID.46mm.OD. BEADED & HA-COATED
SPHC0348	CONSERVE® PLUS CUP 38mm.ID.48mm.OD. BEADED & HA-COATED
SPHC0350	CONSERVE® PLUS CUP 40mm.ID.50mm.OD. BEADED & HA-COATED
SPHC0352	CONSERVE® PLUS CUP 42mm.ID.52mm.OD. BEADED & HA-COATED
SPHC0354	CONSERVE® PLUS CUP 44mm.ID.54mm.OD. BEADED & HA-COATED
SPHC0356	CONSERVE® PLUS CUP 46mm.ID.56mm.OD. BEADED & HA-COATED
SPHC0358	CONSERVE® PLUS CUP 48mm.ID.58mm.OD. BEADED & HA-COATED
SPHC0360	CONSERVE® PLUS CUP 50mm.ID.60mm.OD. BEADED & HA-COATED
SPHC0362	CONSERVE® PLUS CUP 52mm.ID.62mm.OD. BEADED & HA-COATED
SPHC0364	CONSERVE® PLUS CUP 54mm.ID.64mm.OD. BEADED & HA-COATED
38023642	CONSERVE® THIN SHELL36mm ID 42mm OD BEADED
38023844	CONSERVE® THIN SHELL38mm ID 44mm OD BEADED
38024046	CONSERVE® THIN SHELL40mm ID 46mm OD BEADED
38024248	CONSERVE® THIN SHELL42mm ID 48mm OD BEADED
38024450	CONSERVE® THIN SHELL44mm ID 50mm OD BEADED
38024652	CONSERVE® THIN SHELL46mm ID 52mm OD BEADED
38024854	CONSERVE® THIN SHELL48mm ID 54mm OD BEADED
38025056	CONSERVE® THIN SHELL50mm ID 56mm OD BEADED
38025258	CONSERVE® THIN SHELL52mm ID 58mm OD BEADED
38025460	CONSERVE® THIN SHELL54mm ID 60mm OD BEADED
38025662	CONSERVE® THIN SHELL56mm ID 62mm OD BEADED
38025664	CONSERVE® THIN SHELL56mm ID 64mm OD BEADED
38HA3642	CONSERVE® THIN SHELL HA COATED36mm ID 42mm OD BEADED
38HA3844	CONSERVE® THIN SHELL HA COATED38mm ID 44mm OD BEADED
38HA4046	CONSERVE® THIN SHELL HA COATED40mm ID 46mm OD BEADED
38HA4248	CONSERVE® THIN SHELL HA COATED42mm ID 48mm OD BEADED
38HA4450	CONSERVE® THIN SHELL HA COATED44mm ID 50mm OD BEADED
38HA4652	CONSERVE® THIN SHELL HA COATED46mm ID 52mm OD BEADED
38HA4854	CONSERVE® THIN SHELL HA COATED48mm ID 54mm OD BEADED
38HA5056	CONSERVE® THIN SHELL HA COATED50mm ID 56mm OD BEADED
38HA5258	CONSERVE® THIN SHELL HA COATED52mm ID 58mm OD BEADED
38HA5460	CONSERVE® THIN SHELL HA COATED54mm ID 60mm OD BEADED
38HA5662	CONSERVE® THIN SHELL HA COATED56mm ID 62mm OD BEADED

38HA5664	CONSERVE® THIN SHELL HA COATED56mm ID 64mm OD BEADED
38123844	CONSERVE® THIN SHELL PLASMA38 X 44
38124046	CONSERVE® THIN SHELL PLASMA40 X 46
38124248	CONSERVE® THIN SHELL PLASMA42 X 48
38124450	CONSERVE® THIN SHELL PLASMA44 X 50
38124652	CONSERVE® THIN SHELL PLASMA46 X 52
38124854	CONSERVE® THIN SHELL PLASMA48 X 54
38125056	CONSERVE® THIN SHELL PLASMA50 X 56
38125258	CONSERVE® THIN SHELL PLASMA52 X 58
38125460	CONSERVE® THIN SHELL PLASMA54 X 60
38125662	CONSERVE® THIN SHELL PLASMA56 X 62
38BF3642	CONSERVE® BIOFOAM® CUP36mm ID 42mm OD
38BF3844	CONSERVE® BIOFOAM® CUP38mm ID 44mm OD
38BF4046	CONSERVE® BIOFOAM® CUP40mm ID 46mm OD
38BF4248	CONSERVE® BIOFOAM® CUP42mm ID 48mm OD
38BF4450	CONSERVE® BIOFOAM® CUP44mm ID 50mm OD
38BF4652	CONSERVE® BIOFOAM® CUP46mm ID 52mm OD
38BF4854	CONSERVE® BIOFOAM® CUP48mm ID 54mm OD
38BF5056	CONSERVE® BIOFOAM® CUP50mm ID 56mm OD
38BF5258	CONSERVE® BIOFOAM® CUP52mm ID 58mm OD
38BF5460	CONSERVE® BIOFOAM® CUP54mm ID 60mm OD
38BF5662	CONSERVE® BIOFOAM® CUP56mm ID 62mm OD
38SP3642	CONSERVE® THIN SHELL SPIKED 36mm ID 42mm OD BEADED
38SP3844	CONSERVE® THIN SHELL SPIKED 38mm ID 44mm OD BEADED
38SP4046	CONSERVE® THIN SHELL SPIKED 40mm ID 46mm OD BEADED
38SP4248	CONSERVE® THIN SHELL SPIKED 42mm ID 48mm OD BEADED
38SP4450	CONSERVE® THIN SHELL SPIKED 44mm ID 50mm OD BEADED
38SP4652	CONSERVE® THIN SHELL SPIKED 46mm ID 52mm OD BEADED
38SP5056	CONSERVE® THIN SHELL SPIKED 50mm ID 56mm OD BEADED
38SP5258	CONSERVE® THIN SHELL SPIKED 52mm ID 58mm OD BEADED
38SP5460	CONSERVE® THIN SHELL SPIKED 54mm ID 60mm OD BEADED
38SP5662	CONSERVE® THIN SHELL SPIKED 56mm ID 62mm OD BEADED
38SP5664	CONSERVE® THIN SHELL SPIKED 56mm ID 64mm OD BEADED
38SP4854	CONSERVE® THIN SHELL SPIKED 48mm ID 54mm OD BEADED
36693646	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 36ID 46OD
36693848	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 38ID 48OD
36694050	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 40ID 50OD
36694252	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 42ID 52OD
36694454	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 44ID 54OD
36694656	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 46ID 56OD
36694858	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 48ID 58OD
36695060	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 50ID 60OD
36695242	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 52ID 62OD

36695464	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 54ID 64OD
36695262	LINEAGE® MAGNUM ACETABULAR SHELL SUPERFINISHED 52ID 62OD
LINEAGE® METAL LINER	
Part Number	Description
70102846	LINEAGE® METAL LINER28mm X 46-50mm GROUP 1
70103246	METAL LINEAGE® LINER32mm X 46-50mm GROUP 1
70202852	LINEAGE® METAL LINER28mm X 52-56mm GROUP 2
70203252	LINEAGE® METAL LINER32mm X 52-56mm GROUP 2
70302858	LINEAGE® METAL LINER28mm X 58-62mm GROUP 3
70303258	LINEAGE® METAL LINER32mm X 58-62mm GROUP 3
70402864	LINEAGE® METAL LINER28mm X 64-68mm GROUP 4
70403264	LINEAGE® METAL LINER32mm X 64-68mm GROUP 4
70403664	LINEAGE® METAL LINER36mm X 64-68mm GROUP 4
DYNASTY® METAL LINER	
Part Number	Description
DLCOGA28	DYNASTY®COCR LINER 28MM GROUP A
DLCOGB32	DYNASTY®COCR LINER 32MM GROUP B
DLCOGC36	DYNASTY®COCR LINER 36MM GROUP C
DLCOGD38	DYNASTY®COCR LINER 38MM GROUP D
DLCOGE40	DYNASTY®COCR LINER 40MM GROUP E
DLCOGF42	DYNASTY®COCR LINER 42MM GROUP F
DLCOGG44	DYNASTY®COCR LINER 44MM GROUP G
DLCOGH48	DYNASTY®COCR LINER 48MM GROUP H
DLCOGJ52	DYNASTY®COCR LINER 52MM GROUP J
DLCOGK56	DYNASTY®COCR LINER 56MM GROUP K
PROCOTYL® METAL LINER	
Part Number	Description
PHA04702	RIM-LOCK METAL LINER CRICO 28 GROUP A
PHA04704	RIM-LOCK METAL LINER CRICO 28 GROUP B
PHA04706	RIM-LOCK METAL LINER CRICO 32 GROUP C
PHA04708	RIM-LOCK METAL LINER CRICO 32 GROUP D
PHA04710	RIM-LOCK METAL LINER CRICO 36 GROUP E
PHA04712	RIM-LOCK METAL LINER CRICO 36 GROUP F
PHA04714	RIM-LOCK METAL LINER CRICO 36 GROUP G